


Round cylinder EG-4-10-PK-2

Part number: 15886

FESTO

Micro Pneumatic series



Data sheet

| Feature | Value |
|---|---|
| Stroke | 10 mm |
| Piston diameter | 4 mm |
| Cushioning | No cushioning |
| Assembly position | Any |
| Design structure | Piston Piston rod Cylinder barrel |
| Position detection | No |
| Variants | Single-ended piston rod |
| Working pressure | 3.5 ... 7 bar |
| Mode of operation | single-acting pushing action |
| Operating medium | Compressed air in accordance with ISO8573-1:2010 [7:-:] |
| Corrosion resistance classification CRC | 1 - Low corrosion stress |
| PWIS conformity | VDMA24364-B2-L |
| Ambient temperature | 5 ... 60 °C |
| Theoretical force at 0.6 MPa (6 bar, 87 psi), advance | 4.9 N |
| Theoretical minimum spring return force | 1.5 N |
| Theoretical maximum spring return force | 2.6 N |
| Product weight | 5 g |
| Mounting type | with lock nut |
| Pneumatic connection | PK-2 |
| Materials note | Conforms to RoHS |
| Material cover | High alloy steel |
| Material seals | TPE-U(PU) |
| Material piston rod | High alloy steel |
| Material cylinder barrel | Nickel-plated brass |