


# Compact cylinder DMML-32-25-P-A

Part number: 158604

FESTO

Non-rotating, for proximity sensing, with elastic cushioning rings in end-positions, wide range of mounting options.



## Data sheet

| Feature                                    | Value   |
|--|---|
| Stroke                                     | 25 mm   |
| Piston diameter                            | 32 mm   |
| Cushioning                                 | P: Flexible cushioning rings/plates at both ends                            |
| Assembly position                          | Any   |
| Mode of operation                          | double-acting   |
| Design structure                           | Piston<br>Piston rod<br>Profile barrel                                      |
| Position detection                         | For proximity sensor  |
| Variants                                   | Single-ended piston rod   |
| Protection against torque/guide            | Guide rod with yoke   |
| Working pressure                           | 0.6 ... 10 bar  |
| Operating medium                           | Compressed air in accordance with ISO8573-1:2010 [7:4:4]                    |
| Note on operating and pilot medium         | Lubricated operation possible (subsequently required for further operation) |
| Corrosion resistance classification CRC    | 2 - Moderate corrosion stress   |
| Ambient temperature                        | -20 ... 80 °C   |
| Tightening torque of the drive mounting    | 9 Nm +10 %  |
| Theoretical force at 6 bar                 | 483 N   |
| Theoretical force at 6 bar, return stroke  | 415 N   |
| Theoretical force at 6 bar, advance stroke | 483 N   |
| Mounting type                              | Optional<br>with through hole<br>with internal (female) thread              |
| Pneumatic connection                       | G1/8  |
| Material cover                             | Brass   |
| Material seals                             | TPE-U(PU)   |
| Material housing                           | Wrought Aluminum alloy<br>Anodized  |
| Material piston rod                        | High alloy steel, non-corrosive   |