



# Compressed air reservoir CRVZS-10

Part number: 160237

FESTO



## Data sheet

| Feature                                      | Value  |
|--|--|
| Volume                                       | 10 l   |
| Assembly position                            | Downward condensate drain  |
| Conforms to standard                         | AD 2000 reference sheet  |
| Operating pressure MPa                       | -0.095 ... 1.6 MPa   |
| Working pressure                             | -0.95 ... 16 bar   |
| Operating pressure                           | -13.78 ... 232 psi   |
| Authorization                                | TÜV  |
| CE symbol (see declaration of conformity)    | according to EU printing device guideline                            |
| UKCA marking (see declaration of conformity) | UK regulation for pressure equipment                                 |
| Operating medium                             | Compressed air in accordance with ISO8573-1:2010 [-:--:]<br>Nitrogen |
| Corrosion resistance classification CRC      | 3 - High corrosion stress  |
| PWIS conformity                              | VDMA24364-B1/B2-L  |
| Food-safe                                    | See Supplementary material information                               |
| Medium temperature                           | -10 ... 100 °C   |
| Ambient temperature                          | -10 ... 100 °C   |
| Max. tightening torque, connecting thread    | 130 Nm   |
| Max. tightening torque, condensate drain     | 27 Nm  |
| Product weight                               | 6,459 g  |
| Mounting type                                | with through hole  |
| Condensate drain connection                  | G3/8   |
| Pneumatic connection                         | G1   |
| Materials note                               | Conforms to RoHS   |
| Material of air reservoir                    | High alloy steel, non-corrosive                                      |