


Flat cylinder

DZF-25- -A-P-A-S2


Part number: 161247



Non-rotating, for position sensing, with elastic cushioning rings in end positions. Various mounting options, with or without additional mounting components.



Exemplary representation



Data sheet

Feature	Value
Stroke	1 ... 200 mm
Piston diameter	25 mm Equivalent diameter
Max. angular deflection of piston rod +/-	1 deg
Cushioning	P: Flexible cushioning rings/plates at both ends
Assembly position	Any
Mode of operation	double-acting
Design structure	Piston Piston rod
Position detection	For proximity sensor
Variants	Through piston rod
Protection against torque/guide	Oval piston
Operating pressure MPa	0.1 ... 1 MPa
Working pressure	1 ... 10 bar
Operating medium	Compressed air in accordance with ISO8573-1:2010 [7:4:4]
Note on operating and pilot medium	Lubricated operation possible (subsequently required for further operation)
Corrosion resistance classification CRC	2 - Moderate corrosion stress
PWIS conformity	VDMA24364-B1/B2-L
Ambient temperature	-20 ... 80 °C
Max. torque for protection against rotation	0.5 Nm
Theoretical force at 0.6 MPa (6 bar, 87 psi), retracting	247 N
Theoretical force at 0.6 MPa (6 bar, 87 psi), advance	247 N
Moving mass with 0 mm stroke	40 g
Additional mass factor per 10 mm of stroke	6 g
Additional weight per 10 mm stroke	18 g
Basic weight for 0 mm stroke	168 g
Mounting type	with internal (female) thread with accessories Optional
Pneumatic connection	M5
Material cover	Wrought Aluminum alloy
Material seals	NBR TPE-U(PU)
Material housing	Aluminum Smooth anodized
Material piston rod	High alloy steel, non-corrosive