



Linear actuator DGPL-63- -PPV-A-GF-B

Part number: 161790
Product to be discontinued

For proximity sensing, rodless, with positive-locking connection between piston and actuator and adjustable end-position cushioning at both ends.

Type to be discontinued. Available until 2014. See Support Portal for alternative products.



Data sheet

Feature	Value
Stroke	10 ... 3,000 mm
Piston diameter	63 mm
Cushioning	PPV: Pneumatic cushioning adjustable at both ends YSR: Shock absorber, hard characteristic curve
Assembly position	Any
Guide	Plain-bearing guide
Driver principle	positive-locking (slot)
Position detection	For proximity sensor
Working pressure	1.5 ... 8 bar
Mode of operation	double-acting
Operating medium	Compressed air in accordance with ISO8573-1:2010 [7:::]
Note on operating and pilot medium	Lubricated operation possible (subsequently required for further operation)
Corrosion resistance classification CRC	2
Ambient temperature	-10 ... 60 °C
Cushioning length	30 mm
Theoretical force at 6 bar, return stroke	1,870 N
Theoretical force at 6 bar, advance stroke	1,870 N
Moving mass	4,560 g
Moving mass with 0 mm stroke	4,560 g
Basic weight for 0 mm stroke	13,540 g
Additional mass factor per 10 mm of stroke	181 g
alternative connections	See product drawing
Pneumatic connection	G3/8
Materials information for cover	Aluminum casting coated
Materials information for seals	NBR TPE-U(PU)
Materials information, housing	Aluminum Anodized