


# Flat cylinder DZF-1 5/8"- -P-A

Part number: 164096

FESTO

Non-rotating, for position sensing, with elastic cushioning rings in end positions. Various mounting options, with or without additional mounting components.



## Data sheet

Feature	Value
Stroke	0.04 ... 13 "
Piston diameter	1 5/8"
Max. angular deflection of piston rod +/-	0.6 deg
Cushioning	P: Flexible cushioning rings/plates at both ends
Mode of operation	double-acting
Protection against torque/guide	Oval piston
Operating pressure MPa	0.1 ... 1 MPa
Working pressure	1 ... 10 bar
Operating medium	Compressed air in accordance with ISO8573-1:2010 [7:4:4]
Note on operating and pilot medium	Lubricated operation possible (subsequently required for further operation)
Corrosion resistance classification CRC	2 - Moderate corrosion stress
PWIS conformity	VDMA24364-B1/B2-L
Ambient temperature	-20 ... 80 °C
Theoretical force at 0.6 MPa (6 bar, 87 psi), retracting	633 N
Theoretical force at 0.6 MPa (6 bar, 87 psi), advance	754 N
Moving mass with 0 mm stroke	12 g
Additional mass factor per 10 mm of stroke	9 g
Additional weight per 10 mm stroke	16 g
Basic weight for 0 mm stroke	480 g
Pneumatic connection	1/8 NPT
Material cover	Wrought Aluminum alloy
Material seals	FPM TPE-U(PU)
Material housing	Wrought Aluminum alloy
Material piston rod	High alloy steel