



Solenoid valve

MOEBH-3/2-5,0-B-110AC

Part number: 173081
Product to be discontinued

FESTO

With solenoid coil and manual override, without socket.
Type to be discontinued. Available until 2016. See Support Portal for alternative products.



Data sheet

| Feature | Value |
|---|--|
| Valve function | 3/2 open, monostable |
| Type of actuation | electrical |
| Width | 17.8 mm |
| Standard nominal flow rate | 600 l/min |
| Working pressure | 2 ... 8 bar |
| Design structure | Piston slide |
| Type of reset | mechanical spring |
| Protection class | IP65 |
| Authorization | c UL us - Recognized (OL) |
| Nominal size | 5 mm |
| Grid dimension | 18 mm |
| Exhaust-air function | throttleable |
| Sealing principle | soft |
| Assembly position | Any |
| Manual override | with accessories, detenting |
| Type of piloting | Piloted |
| Pilot air supply | Internal |
| Flow direction | non reversible |
| Freedom from overlap | Yes |
| Note on forced dynamisation | Switching frequency at least once a week |
| b value | 0.38 |
| C value | 2.75 l/sbar |
| Switching time off | 28 ms |
| Switching time on | 10 ms |
| Duty cycle | 100% |
| Characteristic coil data | 110 V AC: 50/60 Hz, pick-up power 3 VA, holding power 2.4 VA |
| Operating medium | Compressed air in accordance with ISO8573-1:2010 [7:4:4] |
| Note on operating and pilot medium | Lubricated operation possible (subsequently required for further operation) |
| CE symbol (see declaration of conformity) | according to EU low voltage guideline |
| Vibration resistance | Transport application test at severity level 1 in accordance with FN 942017-4 and EN 60068-2-6 |
| Shock resistance | Shock test with severity level 2 in accordance with FN 942017-5 and EN 60068-2-27 |
| Corrosion resistance classification CRC | 2 |
| Storage temperature | -20 ... 40 °C |
| Medium temperature | -5 ... 50 °C |
| Sound pressure level | 75 dB(A) |
| Pilot medium | Compressed air in accordance with ISO8573-1:2010 [7:4:4] |
| Ambient temperature | -5 ... 50 °C |
| Product weight | 105 g |
| Electrical connection | Plug |

| Feature | Value |
|---------------------------------|--|
| | Cubic design to EN 175301-803 Design C |
| Mounting type | On subbase |
| Pilot exhaust port 82/84 | Subbase |
| Pilot air port 12 | Subbase |
| Pilot air port 14 | Subbase |
| Pneumatic connection, port 1 | Subbase |
| Pneumatic connection, port 2 | Subbase |
| Pneumatic connection, port 3 | Subbase |
| Materials note | Conforms to RoHS |
| Materials information for seals | HNBR NBR |
| Materials information, housing | Aluminum die cast |