


# Mini slide SLT-20-40-P-A

Part number: 170570

FESTO

with precision heavy-duty ball-bearing guide and adjustable end stops.



## Data sheet

| Feature                                    | Value   |
|--|---|
| Stroke                                     | 40 mm   |
| Adjustable end-position range/length       | 12 mm   |
| Piston diameter                            | 20 mm   |
| Operating mode of drive unit               | Yoke  |
| Cushioning                                 | P: Flexible cushioning rings/plates at both ends                            |
| Assembly position                          | Any   |
| Guide                                      | Ball bearing cage guide   |
| Design structure                           | Yoke kinematics   |
| Position detection                         | For proximity sensor  |
| Working pressure                           | 1 ... 10 bar  |
| Mode of operation                          | double-acting   |
| Operating medium                           | Compressed air in accordance with ISO8573-1:2010 [7:4:4]                    |
| Note on operating and pilot medium         | Lubricated operation possible (subsequently required for further operation) |
| Corrosion resistance classification CRC    | 0 - No corrosion stress   |
| Ambient temperature                        | -20 ... 60 °C   |
| Impact energy in end positions             | 0.4 Nm  |
| Max. force F <sub>y</sub>                  | 930 N   |
| Max. force F <sub>z</sub>                  | 930 N   |
| Max. torque M <sub>x</sub>                 | 10 Nm   |
| Max. torque M <sub>y</sub>                 | 10 Nm   |
| Max. torque M <sub>z</sub>                 | 11 Nm   |
| Theoretical force at 6 bar, return stroke  | 317 N   |
| Theoretical force at 6 bar, advance stroke | 376 N   |
| Moving mass                                | 548 g   |
| Product weight                             | 1,228 g   |
| alternative connections                    | See product drawing   |
| Mounting type                              | with through hole   |
| Pneumatic connection                       | G1/8  |
| Materials note                             | Free of copper and PTFE   |
| Material cover                             | Wrought Aluminum alloy  |
| Material seals                             | HNBR  |
| Material housing                           | Wrought Aluminum alloy  |
| Material piston rod                        | High alloy steel, non-corrosive   |