


Linear actuator DGP-80- -

Part number: 175139
Classic - do not use for new projects



DGP, DGPL.

Modern alternatives can be found by entering the first four characters of the type code in the search field.



Exemplary representation

Data sheet

Overall data sheet – Individual values depend upon your configuration.

Feature	Value
Stroke	10 ... 3,000 mm
Piston diameter	80 mm
Cushioning	PPV: Pneumatic cushioning adjustable at both ends YSR: Shock absorber, hard characteristic curve
Assembly position	Any
Guide	Plain-bearing guide Basic guide Recirculating ball bearing guide
Driver principle	positive-locking (slot)
Position detection	For proximity sensor
Variants	Supply port on both ends Standard slide
Operating pressure MPa	0.15 ... 0.8 MPa
Working pressure	1.5 ... 8 bar
Mode of operation	double-acting
CE symbol (see declaration of conformity)	according to EU-Ex protection guideline (ATEX)
UKCA marking (see declaration of conformity)	To UK EX instructions
ATEX category Gas	II 2G
Explosion ignition protection type Gas	Ex h IIC T4 Gb X
Explosion-proof ambient temperature	-10°C ≤ Ta ≤ +60°C
Operating medium	Compressed air in accordance with ISO8573-1:2010 [7:-:-]
Note on operating and pilot medium	Lubricated operation possible (subsequently required for further operation)
Corrosion resistance classification CRC	0 - No corrosion stress 1 - Low corrosion stress 2 - Moderate corrosion stress
PWIS conformity	VDMA24364-B1/B2-L
Ambient temperature	-10 ... 60 °C
Cushioning length	83 mm
Theoretical force at 0.6 MPa (6 bar, 87 psi), retracting	3,016 N
Theoretical force at 0.6 MPa (6 bar, 87 psi), advance	3,016 N
alternative connections	See product drawing
Pneumatic connection	G1/2
Material cover	Aluminum casting coated
Material seals	NBR TPE-U(PU)
Material housing	Aluminum Anodized