


Round cylinder DSAG-16- -P-A-S6

Part number: 176284

FESTO

End cap with threaded lug, with heat-resistant seals up to 120 °C
This product is only available if ordered from Festo Korea Co. Ltd.



Exemplary representation



Data sheet

| Feature | Value |
|--|---|
| Stroke | 1 ... 250 mm |
| Piston diameter | 16 mm |
| Cushioning | P: Flexible cushioning rings/plates at both ends |
| Working pressure | 1 ... 10 bar |
| Mode of operation | double-acting |
| Operating medium | Compressed air in accordance with ISO8573-1:2010 [7:4:4] |
| Note on operating and pilot medium | Lubricated operation possible (subsequently required for further operation) |
| Corrosion resistance classification CRC | 2 |
| Ambient temperature | -20 ... 120 °C |
| Theoretical force at 6 bar, return stroke | 103.7 N |
| Theoretical force at 6 bar, advance stroke | 120.6 N |
| Moving mass with 0 mm stroke | 35 g |
| Additional weight per 10 mm stroke | 4.9 g |
| Basic weight for 0 mm stroke | 56 g |
| Additional mass factor per 10 mm of stroke | 2.2 g |
| Pneumatic connection | M5 |
| Materials information for cover | Wrought Aluminum alloy |
| Materials information for seals | FPM |
| Materials information, housing | High alloy steel, non-corrosive |
| Materials information for piston rod | High alloy steel, non-corrosive |