


Swivel/linear unit DSL-25- -270-P-S20-CC-KF


Part number: 177230

FESTO

For proximity sensing. Rotary and linear movement can be actuated simultaneously or independently of one another. Rotary movement of 0° - 270° infinitely adjustable.



Exemplary representation



Data sheet

Feature	Value
Cushioning angle	10 deg
Rotation angle adjustment range	270 deg
Stroke	10 ... 100 mm
Piston diameter	25 mm
Swivel angle	246 deg
Cushioning	CC: Shock absorber at both ends P: Flexible cushioning rings/plates at both ends
Assembly position	Any
Fine adjustment	1.5 deg
Mode of operation	double-acting
Design structure	Rotary vane
Position detection	For inductive sensors For proximity sensor
Variants	S20: through, hollow piston rod
Protection against torque/guide	with ball-bearing guide
Operating pressure	2.5 ... 8 bar
Max. impact speed	500 mm/s
Max. swivel frequency at 6 bar	1 Hz
Operating medium	Dried compressed air, lubricated or unlubricated
Ambient temperature	-10 ... 60 °C
Cushioning length	5 mm
Torque at 6 bar	5 Nm
Theoretical force at 6 bar, return stroke	173.5 N
Theoretical force at 6 bar, advance stroke	248 N
Permissible mass moment of inertia	0.0016 kgm ²
Additional weight per 10 mm stroke	67 g
Basic weight for 0 mm stroke	1,750 g
Product weight	1,750 g
Mounting type	Clamped in T-slot with external (male) thread Optional
Pneumatic connection	M5
Materials information for cover	Wrought Aluminum alloy Anodized
Materials information for seals	TPE-U(PU)
Materials information, housing	Wrought Aluminum alloy Smooth anodized
Materials information for piston rod	Heat-treatment steel