



Swivel/linear unit

DSL-40-40-270-P-S20-CC-KF

Part number: 177262

FESTO

For proximity sensing. Rotary and linear movement can be actuated simultaneously or independently of one another. Rotary movement of 0° - 270° infinitely adjustable.



Data sheet

Feature	Value
Cushioning angle	15 deg
Rotation angle adjustment range	270 deg
Stroke	40 mm
Piston diameter	40 mm
Swivel angle	240 deg
Cushioning	CC: Shock absorber at both ends P: Flexible cushioning rings/plates at both ends
Assembly position	Any
Fine adjustment	1.5 deg
Mode of operation	double-acting
Design structure	Rotary vane
Position detection	For inductive sensors For proximity sensor
Variants	S20: through, hollow piston rod
Protection against torque/guide	with ball-bearing guide
Operating pressure	2.5 ... 8 bar
Max. impact speed	500 mm/s
Max. swivel frequency at 6 bar	0.7 Hz
Operating medium	Dried compressed air, lubricated or unlubricated
Ambient temperature	-10 ... 60 °C
Cushioning length	12 mm
Torque at 6 bar	20 Nm
Theoretical force at 6 bar, return stroke	495 N
Theoretical force at 6 bar, advance stroke	603 N
Permissible mass moment of inertia	0.004 kgm ²
Additional weight per 10 mm stroke	175 g
Basic weight for 0 mm stroke	5,350 g
Product weight	5,350 g
Mounting type	Clamped in T-slot with external (male) thread Optional
Pneumatic connection	G1/8
Materials information for cover	Wrought Aluminum alloy Anodized
Materials information for seals	TPE-U(PU)
Materials information, housing	Aluminum Smooth anodized
Materials information for piston rod	Heat-treatment steel