


Liquid separator CQA-22

Part number: 177716

FESTO

For dry air.



Data sheet

Feature	Value
Nominal size	12 mm
Assembly position	Any
Container size	1
Design structure	Push/pull principle
Operating pressure complete temperature range	-0.95 ... 7 bar
Temperature dependent working pressure	-0.95 ... 15 bar
Operating medium	Compressed air in accordance with ISO8573-1:2010 [7::-]
Note on operating and pilot medium	Lubricated operation possible (subsequently required for further operation)
Corrosion resistance classification CRC	2 - Moderate corrosion stress
PWIS conformity	VDMA24364 zone III
Food-safe	See Supplementary material information
Medium temperature	-25 ... 75 °C
Ambient temperature	-25 ... 70 °C
Product weight	76 g
Pneumatic connection, port 1	for tube/piping, 22mm outside diameter
Pneumatic connection, port 2	for piping or tubing with outside diameter 22 mm
Materials note	Conforms to RoHS
Material housing	POM
Material release ring	POM
Material of tube retaining claw	High alloy steel, non-corrosive