


Profile cylinder DNC-1 5/8" - -

Part number: 184818

FESTO

In accordance with ISO 15552.



Data sheet

Overall data sheet – Individual values depend upon your configuration.

Feature	Value
Stroke	0.08 ... 80 "
Piston diameter	1 5/8"
Based on the standard	ISO 15552 (previously also VDMA 24652, ISO 6431, NF E49 003.1, UNI 10290)
Cushioning	P: Flexible cushioning rings/plates at both ends PPV: Pneumatic cushioning adjustable at both ends
Assembly position	Any
Design structure	Piston Piston rod Profile barrel
Position detection	For proximity sensor No
Variants	Extended male piston rod thread Female thread on piston rod Piston rod with special thread Extended piston rod clamping unit on piston rod With protection against rotation Excellent corrosion protection Dust protection Through piston rod Heat resistant seals, max. 120°C Single-ended piston rod
Protection against torque/guide	Square piston rod
Operating pressure MPa	0.06 ... 1.2 MPa
Working pressure	0.6 ... 12 bar
Mode of operation	double-acting
Operating medium	Compressed air in accordance with ISO8573-1:2010 [7:4:4]
Note on operating and pilot medium	Lubricated operation possible (subsequently required for further operation)
Corrosion resistance classification CRC	2 - Moderate corrosion stress 3 - High corrosion stress
PWIS conformity	VDMA24364-B1/B2-L
Ambient temperature	-20 ... 120 °C
Impact energy in end positions	0.2 J
Max. torque for protection against rotation	1.1 Nm
Theoretical force at 0.6 MPa (6 bar, 87 psi), retracting	633 N
Theoretical force at 0.6 MPa (6 bar, 87 psi), advance	633 ... 754 N
Moving mass with 0 mm stroke	307 g
Additional mass factor per 10 mm of stroke	16 g
Basic weight for 0 mm stroke	800 g
Additional weight per 10 mm stroke	45 g

Feature	Value
Mounting type	with internal (female) thread with accessories
Pneumatic connection	NPT1/4-18
Materials note	Conforms to RoHS
Material cover	Aluminum die cast coated
Material cylinder barrel	Wrought Aluminum alloy Smooth anodized