


Guide cylinder DFP-16-80-P-A

Part number: 186735
Product to be discontinued

FESTO

Protected against torsion, for proximity sensing.

Type to be discontinued. Available until 2018. See Support Portal for alternative products.



Data sheet

Feature	Value
Stroke	80 mm
Piston diameter	16 mm
Cushioning	P: Flexible cushioning rings/plates at both ends
Assembly position	Any
Guide	Recirculating ball bearing guide
Design structure	Guide
Position detection	For proximity sensor
Working pressure	1 ... 10 bar
Max. speed	0.8 m/s
Mode of operation	double-acting
Operating medium	Compressed air in accordance with ISO8573-1:2010 [7:4:4]
Note on operating and pilot medium	Lubricated operation possible (subsequently required for further operation)
Corrosion resistance classification CRC	0 - No corrosion stress
Ambient temperature	-10 ... 60 °C
Impact energy in end positions	0.07 Nm
Theoretical force at 6 bar, return stroke	91 N
Theoretical force at 6 bar, advance stroke	121 N
Moving mass	75 g
Product weight	263 g
Pneumatic connection	M5
Materials note	Free of copper and PTFE
Material cover	Wrought Aluminum alloy
Material seals	NBR
Material housing	Wrought Aluminum alloy
Material piston rod	Heat-treatment steel