

Solenoid valve


MN2H-2X30-G-D-02-S-110VAC

Part number: 191391

FESTO

In accordance with ISO 15407/-1, with solenoid coil and manual override, without plug socket.

Type to be discontinued. Available until 2009.



Data sheet

Feature	Value
Valve function	2x3/2 open, single solenoid
Type of actuation	electrical
Width	18 mm
Standard nominal flow rate	490 l/min
Working pressure	2 ... 10 bar
Design structure	Piston slide
Type of reset	Air spring
Protection class	IP65
Authorization	Germanischer Lloyd
Nominal size	6 mm
Grid dimension	19 mm
Exhaust-air function	throttleable
Sealing principle	soft
Assembly position	Any
Conforms to standard	VDMA 24563
Manual override	with accessories, detenting
Type of piloting	Piloted
Pilot air supply	external
Flow direction	non reversible
Pilot pressure	1.3 ... 10 bar
b value	0.25
C value	2.15 l/sbar
Switching time off	16 ms
Switching time on	15 ms
Characteristic coil data	110V AC: 50Hz 110V AC: 60Hz
Operating medium	filtered compressed air, grade of filtration 40 µm, lubricated or unlubricated Vacuum
CE symbol (see declaration of conformity)	according to EU low voltage guideline
Corrosion resistance classification CRC	2
Medium temperature	-10 ... 50 °C
Pilot medium	filtered compressed air, grade of filtration 40 µm, lubricated or unlubricated
Ambient temperature	-10 ... 50 °C
Product weight	210 g
Electrical connection	Plug to DIN 43650 Design C
Mounting type	with through hole
Auxiliary pilot air port 12/14	Subbase VDMA 24563 size 2
Pilot exhaust port 82/84	Subbase VDMA 24563 size 2

Feature	Value
Pneumatic connection, port 1	Subbase VDMA 24563 size 2
Pneumatic connection, port 2	Subbase VDMA 24563 size 2
Pneumatic connection, port 3	Subbase VDMA 24563 size 2
Pneumatic connection, port 4	Subbase VDMA 24563 size 2
Pneumatic connection, port 5	Subbase VDMA 24563 size 2
Materials information for seals	NBR
Materials information, housing	Aluminum die cast