


# Vacuum generator

## VN-05-N-I3-PQ2-VT2

Part number: 193637

FESTO

In-line, high suction rate, width 14 mm, with plug connector and push-in sleeve.



## Data sheet

Feature	Value
Nominal size, Laval nozzle	0.45 mm
Grid dimension	13 mm
Assembly position	Any
Ejector characteristic	High suction flow rate Inline
Design structure	Straight design
Working pressure for max. suction rate	6 bar
Working pressure	1 ... 8 bar
Nominal working pressure	6 bar
Max. suction rate with respect to atmosphere	12 l/min
Air supply time at nominal working pressure	1.57 s
Operating medium	Compressed air in accordance with ISO8573-1:2010 [7:4:4]
Note on operating and pilot medium	Lubricated operation not possible
Corrosion resistance classification CRC	1 - Low corrosion stress
PWIS conformity	VDMA24364-B1/B2-L
Medium temperature	0 ... 60 °C
Ambient temperature	0 ... 60 °C
Product weight	12 g
Mounting type	Line installation
Pneumatic connection, port 1	QS-6
Pneumatic connection, port 3	Non-ducted
Vacuum connection	Push-in sleeve QS-6
Materials note	Conforms to RoHS
Material seals	NBR
Material receiver nozzle	POM
Material housing	POM-reinforced
Material transmitter nozzle	Wrought Aluminum alloy
Material fitting	Brass Nickel plated