


# Round cylinder ESNU-32-50-P

Part number: 195872

FESTO

As per DIN ISO 6432, with elastic cushioning rings in end positions.  
Various mounting options, with or without additional mounting components.



## Data sheet

Feature	Value
Stroke	50 mm
Piston diameter	32 mm
Piston rod thread	M10x1,25
Cushioning	P: Flexible cushioning rings/plates at both ends
Assembly position	Any
Design structure	Piston Piston rod Cylinder barrel
Operating pressure MPa	0.12 ... 1 MPa
Working pressure	1.2 ... 10 bar
Mode of operation	single-acting pushing action
Operating medium	Compressed air in accordance with ISO8573-1:2010 [7:4:4]
Note on operating and pilot medium	Lubricated operation possible (subsequently required for further operation)
Corrosion resistance classification CRC	2 - Moderate corrosion stress
Ambient temperature	-20 ... 80 °C
Spring return force, retracted	20 N
Theoretical force at 0.6 MPa (6 bar, 87 psi), retracting	20 N
Theoretical force at 0.6 MPa (6 bar, 87 psi), advance	442.2 N
Moving mass	166 g
Moving mass with 0 mm stroke	121 g
Additional weight per 10 mm stroke	15.5 g
Basic weight for 0 mm stroke	370.5 g
Product weight	448 g
Additional mass factor per 10 mm of stroke	9 g
Mounting type	with accessories
Pneumatic connection	G1/8
Materials note	Conforms to RoHS
Material cover	Wrought Aluminum alloy
Material seals	NBR TPE-U(PU)
Material piston rod	High alloy steel
Material cylinder barrel	High alloy steel, non-corrosive