

# Standards-based cylinder DNC-80-20-PPV-A

Part number: 1922641

Classic - do not use for new projects

Modern alternatives can be found by entering the first four characters of the type code in the search field.

FESTO



## Data sheet

| Feature  | Value   |
|--|---|
| Stroke   | 20 mm   |
| Piston diameter  | 80 mm   |
| Piston rod thread  | M20x1,5   |
| Cushioning   | PPV: Pneumatic cushioning adjustable at both ends                           |
| Assembly position  | Any   |
| Conforms to standard                                     | ISO 15552   |
| Piston-rod end   | Male thread   |
| Design structure   | Piston<br>Piston rod<br>Profile barrel                                      |
| Position detection                                       | For proximity sensor  |
| Variants   | Single-ended piston rod   |
| Operating pressure MPa                                   | 0.06 ... 1.2 MPa  |
| Working pressure   | 0.6 ... 12 bar  |
| Mode of operation  | double-acting   |
| Operating medium   | Compressed air in accordance with ISO8573-1:2010 [7:4:4]                    |
| Note on operating and pilot medium                       | Lubricated operation possible (subsequently required for further operation) |
| Corrosion resistance classification CRC                  | 2 - Moderate corrosion stress   |
| PWIS conformity  | VDMA24364-B1/B2-L   |
| Ambient temperature                                      | -20 ... 80 °C   |
| Impact energy in end positions                           | 0.9 J   |
| Cushioning length  | 32 mm   |
| Theoretical force at 0.6 MPa (6 bar, 87 psi), retracting | 2,721 N   |
| Theoretical force at 0.6 MPa (6 bar, 87 psi), advance    | 3,016 N   |
| Moving mass with 0 mm stroke                             | 1,131 g   |
| Additional mass factor per 10 mm of stroke               | 38 g  |
| Basic weight for 0 mm stroke                             | 2,790 g   |
| Additional weight per 10 mm stroke                       | 106 g   |
| Mounting type  | with internal (female) thread<br>with accessories                           |
| Pneumatic connection                                     | G3/8  |
| Materials note   | Conforms to RoHS  |
| Material cover   | Aluminum die cast<br>coated   |
| Material seals   | TPE-U(PU)   |
| Material piston rod                                      | High alloy steel  |
| Material cylinder barrel                                 | Wrought Aluminum alloy<br>Smooth anodized                                   |