

# Liquid separator CQA-28

Part number: 196984

FESTO

For dry air.



## Data sheet

Feature	Value
Nominal size	20 mm
Assembly position	Vertical
Container size	1
Design structure	Push/pull principle
Operating pressure complete temperature range	-0.95 ... 7 bar
Temperature dependent working pressure	-0.95 ... 10 bar
Operating medium	Compressed air in accordance with ISO8573-1:2010 [7::-]
Note on operating and pilot medium	Lubricated operation possible (subsequently required for further operation)
Corrosion resistance classification CRC	2 - Moderate corrosion stress
PWIS conformity	VDMA24364 zone III
Medium temperature	-25 ... 75 °C
Ambient temperature	-25 ... 70 °C
Product weight	18 g
Pneumatic connection, port 1	Push-in sleeve CQ-28
Pneumatic connection, port 2	Push-in sleeve CQ-28
Materials note	Conforms to RoHS
Material housing	Brass