


Valve manifold CDVI5.0

Part number: 197648

FESTO

Valve manifold CDVI, Clean Design.



Data sheet

Overall data sheet – Individual values depend upon your configuration.

Feature	Value
Valve function	3/2 closed, monostable 3/2 open/closed, monostable 3/2 open, monostable 2/2 open, monostable 2/2 closed, monostable 5/3 closed 5/3 exhausted 5/3 pressurized 5/2 bistable 2x3/2 closed, monostable 2x3/2 open, monostable 5/2 monostable
Valve size	24 mm
Max. standard nominal flow rate	650 l/min at 24 mm
Working pressure	-0.9 ... 10 bar
Authorization	C-Tick
Based on the standard	ISO 14159 EN 1672-2
Nominal operating voltage DC	24 V
Permissible voltage fluctuation	+/- 10 %
CE symbol (see declaration of conformity)	according to EU-EMV guideline
Corrosion resistance classification CRC	3
Medium temperature	-5 ... 50 °C
Protection class	IP65 IP67 IP66 NEMA 4
Ambient temperature	-5 ... 50 °C
Electrical connection	Multi-pin plug Fieldbus
Switching position indicator	LED
Materials note	Conforms to RoHS
Type of actuation	electrical
Electrical I/O system	Yes
Valve manifold type	15
Max. number of valve positions	16
Valve manifold structure	modular