

Axial kit EAMM-A-D60-60H-S1

Part number: 2256697

FESTO

Suitable for electric drives.



Data sheet

Feature	Value
Assembly position	Any
PWIS conformity	VDMA24364 zone III
Storage temperature	-25 ... 60 °C
Relative air humidity	0 - 95 %
Protection class	IP40
Ambient temperature	-10 ... 60 °C
No-load driving torque	1 Nm
Transferable torque	17 Nm
Product weight	1,250 g
Interface code, actuator	D60A D60B
Interface code, motor in	60H
Materials note	Conforms to RoHS