


# Standard cylinder DNG-50- -PPV-A-S6

Part number: 34856

FESTO

As per ISO 15552, NF E 49 003.1 and UNI 10 290, for proximity sensing,  
with adjustable cushioning at both ends.



Exemplary representation



## Data sheet

Feature	Value
Stroke	1 ... 2,000 mm
Piston diameter	50 mm
Piston rod thread	M16x1,5
Cushioning	PPV: Pneumatic cushioning adjustable at both ends
Assembly position	Any
Conforms to standard	ISO 15552 (previously also VDMA 24652, ISO 6431, NF E49 003.1, UNI 10290)
Piston-rod end	Male thread
Design structure	Piston Piston rod
Position detection	For proximity sensor
Variants	Heat resistant seals, max. 120°C
Working pressure	0.6 ... 12 bar
Mode of operation	double-acting
Operating medium	Compressed air in accordance with ISO8573-1:2010 [7:4:4]
Note on operating and pilot medium	Lubricated operation possible (subsequently required for further operation)
Corrosion resistance classification CRC	2
Ambient temperature	0 ... 120 °C
Authorization	Germanischer Lloyd
Cushioning length	23 mm
Theoretical force at 6 bar, return stroke	990 N
Theoretical force at 6 bar, advance stroke	1,178 N
Additional weight per 10 mm stroke	50 g
Basic weight for 0 mm stroke	1,400 g
Mounting type	with accessories
Pneumatic connection	G1/4
Materials information for cover	Aluminum
Materials information for seals	NBR TPE-U(PU)
Materials information for piston rod	High alloy steel
Materials information for cylinder barrel	Wrought Aluminum alloy