


# Mini slide

## SLT-20-100-A-CC-B

Part number: 197906

FESTO

with precision heavy-duty ball-bearing guide and shock absorbers.



## Data sheet

Feature	Value
Stroke	100 mm
Adjustable end-position range/length	12 mm
Piston diameter	20 mm
Operating mode of drive unit	Yoke
Cushioning	CC: Shock absorber at both ends
Assembly position	Any
Guide	Ball bearing cage guide
Design structure	Yoke kinematics
Position detection	For proximity sensor
Working pressure	1 ... 10 bar
Repetition accuracy	0.02 mm
Mode of operation	double-acting
Operating medium	Compressed air in accordance with ISO8573-1:2010 [7:4:4]
Note on operating and pilot medium	Lubricated operation possible (subsequently required for further operation)
Corrosion resistance classification CRC	0 - No corrosion stress
Ambient temperature	-20 ... 60 °C
Impact energy in end positions	3 Nm
Cushioning length	8 mm
Max. force F <sub>y</sub>	1,160 N
Max. force F <sub>z</sub>	1,160 N
Max. torque M <sub>x</sub>	18 Nm
Max. torque M <sub>y</sub>	18 Nm
Max. torque M <sub>z</sub>	11 Nm
Theoretical force at 6 bar, return stroke	317 N
Theoretical force at 6 bar, advance stroke	376 N
Moving mass	2,088 g
Product weight	2,128 g
alternative connections	See product drawing
Mounting type	with through hole
Pneumatic connection	G1/8
Materials note	Free of copper and PTFE
Material cover	Wrought Aluminum alloy
Material seals	HNBR
Material housing	Wrought Aluminum alloy
Material piston rod	High alloy steel, non-corrosive