


Coupling

EAMD-67-51-20-32X32-U

Part number: 3717812

FESTO

drive component, which transmits the rotary motion of a stepper or servo motor



Data sheet

| Feature | Value |
|------------------------|-----------------------|
| Holder diameter 1 | 20 mm |
| Holder diameter 2 | 32 mm |
| Size | 67 |
| Nominal length | 51 mm |
| Assembly position | Any |
| Max. speed | 4,500 1/min |
| PWIS conformity | VDMA24364-B2-L |
| Storage temperature | -25 ... 60 °C |
| Relative air humidity | 0 - 95 % |
| Ambient temperature | -25 ... 60 °C |
| Mass moment of inertia | 374 kgmm ² |
| Transferable torque | 120 Nm |
| Product weight | 744 g |
| Materials note | Conforms to RoHS |