

limit switch box

SRBE-CA3-YR90-N-20N-ZC-C2N12-C1

Part number: 3998919

FESTO

For electrical feedback and position monitoring of process valves actuated with pneumatic quarter turn actuators, inductive measuring principle.



Data sheet

Feature	Value
Design	Angular
Based on the standard	EN 60947-5-6 ISO 5211 VDI/VDE 3845
Authorization	RCM Mark
CE symbol (see declaration of conformity)	according to EU-EMV guideline in accordance with EU RoHS directive
Explosion ignition protection type Gas	AEx nA IIC T5 Gc Ex nA IIC T5 Gc
Explosion ignition protection type Dust	AEx tb IIIC T108°C Db Ex tb IIIC T108°C Db
Explosion protection certification outside the EU	Class I, Div. 1 (CA) Class I, Div. 1 (US) Class I, Div. 2 (CA) Class I, Div. 2 (US) Class II, Div. 1 (CA) Class II, Div. 1 (US) Class III (CA) Class III (US) EPL Db (CA) EPL Db (US) EPL Gb (CA) EPL Gb (US) EPL Gc (CA) EPL Gc (US)
Explosion-proof ambient temperature	-20°C ≤ Ta ≤ +60°C
Certificate issuing department	CSA 263311
Materials note	Conforms to RoHS
Safety Integrity Level (SIL)	SIL 2
Measuring principle	Inductive
Ambient temperature	-20 ... 60 °C
Switch output	NAMUR
Switching element function	Normally closed contact
Max. output current DC	3 mA
Operating voltage range DC	8.2 V
Electrical connection	10-pin Screwed terminal
Connectable nominal conductor cross section	0.25 ... 2.5 mm ²
Cable gland connection	1/2 NPT
Mounting type	On flange to ISO 5211 With mounting bracket
Connection for positioner and position sensor conforms to standard	VDI/VDE 3845 size AA 1
Assembly position	Any

Feature	Value
Product weight	1,700 g
Housing color	silver
Material housing	Die-cast aluminium, painted
Material seals	NBR
Material shaft	High alloy steel, non-corrosive
Material screws	High alloy steel, non-corrosive
Material mounting bracket	High alloy steel, non-corrosive
Material indicator	PC
Material snap ring	High alloy steel, non-corrosive
Material disc	High alloy steel, non-corrosive
Position indicator	Yellow/red
Setting range, angle recording	0 ... 90 deg
Storage temperature	-20 ... 60 °C
Protection class	IP67 NEMA 4/4X
Shock resistance	Shock test with severity level 2 in accordance with FN 942017-5 and EN 60068-2-27
Vibration resistance	Transport application test at severity level 2 in accordance with FN 942017-4 and EN 60068-2-6
PWIS conformity	VDMA24364 zone III
Degree of contamination	3