


Solenoid coil

MSFW-24-50/60

Part number: 4534

FESTO

With standard plug socket



Data sheet

Feature	Value
Assembly position	Any
Switching position indicator	No
Min. pickup time	10 ms
Duty cycle	100 %
Power factor cos {phi}	0.7
Characteristic coil data	24 V AC: 50/60 Hz, pick-up power 9 VA, holding power 7 VA
Permissible frequency fluctuation	+/- 5 %
Permissible voltage fluctuation	+/- 10 %
PWIS conformity	VDMA24364-C1-L
Protection class	IP65
Ambient temperature	-5 ... 40 °C
Max. tightening torque, plug socket	0.4 Nm
Product weight	55 g
Electrical connection	3-pin Plug vanes for MSSD-F
Mounting type	With knurled nut
Materials note	Conforms to RoHS
Material solenoid coil	Duroplast Copper Steel
Material winding	Copper