

# Spindle axis


## EGC-120-300-BS-10P-KF-0H-ML-GK

Part number: 3013573

★ Core product range

With recirculating ball bearing guide

FESTO



## Data sheet

Feature	Value
Working stroke	300 mm
Size	120
Stroke reserve	0 mm
Spindle diameter	25 mm
Spindle pitch	10 mm/U
Assembly position	Any
Guide	Recirculating ball bearing guide
Design structure	Electromechanical linear axis with recirculating ball bearing spindle
Motor type	Stepper motor Servomotor
Spindle type	Ball screw actuator
Max. acceleration	15 m/s <sup>2</sup>
Max. speed	0.6 ... 0.75 m/s
Repetition accuracy	±0,02 mm
Duty cycle	100 %
PWIS conformity	VDMA24364-B2-L
Protection class	IP40
Ambient temperature	-10 ... 60 °C
Area moment of inertia 2nd degree Ix	5,010E+03 mm <sup>4</sup>
Area moment of inertia 2nd degree Iy	5,820E+03 mm <sup>4</sup>
Area moment of inertia 2nd degree Iz	5,010E+03 mm <sup>4</sup>
Max. force Fy	6,890 N
Max. force Fz	6,890 N
Max. torque Mx	144 Nm
Max. radial force at drive shaft	500 N
Max. feed force Fx	1,500 N
Torsional mass moment of inertia It	1,430E+03 mm <sup>4</sup>
Mass moment of inertia JH per meter of stroke	2.756 kgcm <sup>2</sup>
Feed constant	10 mm/U
Material of end caps	Wrought Aluminum alloy Anodized
Material of moment compensator	Wrought Aluminum alloy Anodized
Material of profile	Wrought Aluminum alloy Anodized
Materials note	Conforms to RoHS
Material drive cover	Wrought Aluminum alloy Anodized
Material guide slide	Steel
Material guide rail	Steel
Material slide	Wrought Aluminum alloy Anodized
Material spindle nut	Steel
Material spindle	Steel