


# Linear actuator SLM-16- -KF-A

Part number: 32782

FESTO

Centering pins or centering sleeves are included with the linear unit.  
Cylinder sensor SIEN-... can be ordered from the modular system using  
order code PV, PH, NV, NH. Can also be ordered as a separate part.



## Data sheet

Overall data sheet – Individual values depend upon your configuration.

Feature	Value
Stroke	10 ... 800 mm
Piston diameter	16 mm
Cushioning	P: Flexible cushioning rings/plates at both ends YSR: Shock absorber, hard characteristic curve
Assembly position	Any
Guide	Recirculating ball bearing guide
Position detection	For proximity sensor For inductive sensors
Variants	basic design Hollow guide rod Hollow guide rod and reversing plate
Operating pressure MPa	0.7 MPa
Working pressure	7 bar
Mode of operation	double-acting
Operating medium	Compressed air in accordance with ISO8573-1:2010 [7:-:-]
Note on operating and pilot medium	Lubricated operation possible (subsequently required for further operation)
Corrosion resistance classification CRC	1 - Low corrosion stress
PWIS conformity	VDMA24364-B2-L
Ambient temperature	-20 ... 60 °C
Theoretical force at 0.6 MPa (6 bar, 87 psi), retracting	121 N
Theoretical force at 0.6 MPa (6 bar, 87 psi), advance	121 N
Moving mass	1,080 g
Additional mass factor per 10 mm of stroke	15 g
Basic weight for 0 mm stroke	1,730 g
Additional weight per 10 mm stroke	15 g
Pneumatic connection	M5
Material cover	Aluminum
Material seals	PA TPE-U(PU)
Material housing	Aluminum