


Bus node CPX-FB11

Part number: 526172
Product to be discontinued

for modular electrical terminal CPX.

FESTO



Data sheet

Feature	Value
Protocol	DeviceNet
Dimensions W x L x H	(including interlinking block) 50 mm x 107 mm x 50 mm
Product weight	120 g
Ambient temperature	-5 ... 50 °C
Storage temperature	-20 ... 70 °C
Protection class	IP65 IP67
Corrosion resistance classification CRC	1 - Low corrosion stress
PWIS conformity	VDMA24364-B2-L
Material housing	PA-reinforced PC
Product-specific LED display	M: Modify, parameterization PL: load supply PS: Electronics supply, sensor supply SF: system error
Bus-specific LED display	IO: I/O status MS: Module status NS: Network status
Device-specific diagnostics	Channel and module-oriented diagnostics Undervoltage modules Diagnostics memory
Control elements	DIL switches
Fieldbus interface	Sub-D socket, 9-pin Sub-D plug, for self-assembly MicroStyle: 2x M12x1, 5-pin OpenStyle: 5-pin terminal strip
Maximum address volume for inputs	64 Byte
Maximum address volume for outputs	64 Byte
Parameters configuring	Diagnostics behaviour Fail-safe reaction Forcing of channels Idle mode characteristics Signal setup System parameters
Baud rate	125, 250, 500 kbit/s
Configuration support	EDS file
Additional functions	- Acyclic data access via "Explicit Message" Channel-oriented diagnostics via fieldbus Quickconnect Start-up parameterization in normal text via fieldbus System status can be represented using process data Additional diagnostics interface for operator units
Operating voltage range DC	18 ... 30 V

Feature	Value
Nominal operating voltage DC	24 V
Intrinsic current consumption at operating voltage	Typ. 200 mA
Communication types	Change of State Cyclic Explicit Message Strobed I/O Polled I/O