

# Lubricator LOE-QS4-D-MICRO



Part number: 526313  
Classic - do not use for new projects

FESTO

Connection plate with push-in connector

Modern alternatives can be found by entering the first four characters of the type code in the search field.

Type to be discontinued. Available until 2023. See Support Portal for alternative products.



## Data sheet

Feature	Value
Size	Micro
Series	D
Assembly position	Vertical +/- 5°
Design structure	proportional standard mist lubricator
Max. oil capacity	6.5 cm <sup>3</sup>
Working pressure	1 ... 10 bar
Minimum flow rate for lubricator function	3 l/min
Standard nominal flow rate	160 l/min
Operating medium	Compressed air in accordance with ISO8573-1:2010 [7:4:4] Inert gases
Note on operating and pilot medium	Lubricated operation possible (subsequently required for further operation)
Corrosion resistance classification CRC	2 - Moderate corrosion stress
Storage temperature	-10 ... 60 °C
Air purity class at output	Compressed air in accordance with ISO8573-1:2010 [7:4:-] Inert gases
Medium temperature	-10 ... 60 °C
Ambient temperature	-10 ... 60 °C
Product weight	59 g
Mounting type	Line installation with accessories Optional
Pneumatic connection, port 1	QS-4
Pneumatic connection, port 2	QS-4
Materials note	Conforms to RoHS
Material housing	Aluminum die cast
Material bowl	PC