

# Linear actuator DLGF-G-32-200-PPSA

Part number: 5074782

FESTO



## Data sheet

Feature	Value
Stroke	200 mm
Piston diameter	32 mm
Cushioning	PPS: Self-adjusting pneumatic end-position cushioning
Assembly position	Any
Guide	Basic guide
Driver principle	positive-locking (slot)
Position detection	For proximity sensor
Operating pressure MPa	0.15 ... 0.8 MPa
Working pressure	1.5 ... 8 bar
Mode of operation	double-acting
Operating medium	Compressed air in accordance with ISO8573-1:2010 [7:-:-]
Note on operating and pilot medium	Lubricated operation possible (subsequently required for further operation)
Corrosion resistance classification CRC	1 - Low corrosion stress
PWIS conformity	VDMA24364-B1/B2-L
Ambient temperature	0 ... 60 °C
Cushioning length	11.6 mm
Max. force F <sub>y</sub>	0 N
Max. force F <sub>z</sub> (towards drive)	276 N
Max. force +F <sub>z</sub> (away from drive)	138 N
Max. torque M <sub>x</sub>	1.8 Nm
Max. torque M <sub>y</sub>	7.6 Nm
Max. torque M <sub>z</sub>	2.9 Nm
Theoretical force at 0.6 MPa (6 bar, 87 psi), retracting	483 N
Theoretical force at 0.6 MPa (6 bar, 87 psi), advance	483 N
Moving mass	208 g
Product weight	2,798 g
alternative connections	See product drawing
Mounting type	Direct mounting via through-holes with accessories
Pneumatic connection	G1/8
Materials note	Conforms to RoHS Free of copper
Material cover	Coated die-cast aluminium
Material seals	NBR TPE-U(PU)
Material housing	Anodised aluminium