

Lubricator MS6N-LOE

Part number: 527675

FESTO

With NPT thread



Exemplary representation

Data sheet

Overall data sheet – Individual values depend upon your configuration.

Feature	Value
Size	6
Series	MS
Assembly position	Vertical +/- 5°
Design structure	proportional standard mist lubricator
Bowl guard	Plastic guard integrated as metal shell
Working pressure	1 ... 16 bar
Minimum flow rate for lubricator function	50 l/min
Standard nominal flow rate	2,500 ... 7,200 l/min
Authorization	c UL us - Recognized (OL)
Operating medium	Compressed air in accordance with ISO8573-1:2010 [7:4:4] Inert gases
Note on operating and pilot medium	Lubricated operation possible
Corrosion resistance classification CRC	2 - Moderate corrosion stress
PWIS conformity	VDMA24364-B1/B2-L
Storage temperature	-10 ... 60 °C
Food-safe	See Supplementary material information
Medium temperature	-10 ... 60 °C
Oil viscosity	ISO VG 32
Ambient temperature	-10 ... 60 °C
Mounting type	Line installation with accessories Optional
Materials note	Conforms to RoHS
Material housing	Aluminum die cast