


Compact cylinder AEN-S-50-10-I-P

Part number: 5137801

FESTO



Data sheet

Feature	Value
Stroke	10 mm
Piston diameter	50 mm
Cushioning	Elastic cushioning rings/pads at both ends
Mounting position	Any
Mode of operation	Pushing
Piston rod end	Internal thread
Structural design	Piston Piston rod
Variants	Additional PTFE piston guide
Operating pressure	0.1 MPa...1 MPa 1 bar...10 bar 14.5 psi...145 psi
Operating medium	Compressed air as per ISO 8573-1:2010 [7:4:4]
Information on operating and pilot media	Operation with oil lubrication possible (required for further use)
Corrosion resistance class (CRC)	1 - Low corrosion stress
LABS (PWIS) conformity	VDMA24364-B2-L
Cleanroom suitability, measured according to ISO 14644-14	Class 5 according to ISO 14644-1
Ambient temperature	0 °C...80 °C
Impact energy in the end positions	0.6 J
Theoretical force at 6 bar, retracting	66.2 N
Theoretical force at 6 bar, advancing	1178 N
Moving mass at 0 mm stroke	105 g
Additional moving mass per 10 mm stroke	16 g
Basic weight with 0 mm stroke	310 g
Additional weight per 10 mm stroke	63 g
Type of mounting	Optionally: With through-hole With internal thread With accessories
Pneumatic connection	G1/8
Note on materials	RoHS-compliant
Cover material	Wrought aluminum alloy, anodized
Material of dynamic seals	NBR

Feature	Value
Housing material	Wrought aluminum alloy, anodized
Piston rod material	High-alloy stainless steel