


Servomotor EMMB-AS-60-02-K-S

Part number: 5219177

FESTO



Data sheet

Feature	Value
Ambient temperature	-20 ... 40 °C
Storage temperature	-20 ... 70 °C
Relative air humidity	0 - 90 %
Conforms to standard	IEC 60034
Insulation protection class	F
Rating class according to EN 60034-1	S1
Protection class	IP65
Shaft design Woodruff key	DIN 6885 A 5 x 5 x 16
Electrical connector system	Plug
Materials note	Contains PWIS substances Conforms to RoHS
Corrosion resistance classification CRC	0 - No corrosion stress
CE symbol (see declaration of conformity)	according to EU-EMV guideline according to EU low voltage guideline
Authorization	c UL us - Recognized (OL)
Nominal operating voltage DC	300 V
Nominal voltage DC	300 V
Standstill torque	0.7 Nm
Nominal torque	0.64 Nm
Peak torque	1.92 Nm
Nominal rotary speed	3,000 1/min
Max. speed	6,000 1/min
Nominal motor power	200 W
Continuous open-circuit current	1.5 A
Nominal motor current	1.4 A
Peak current	4.2 A
Motor constant	0.48 Nm/A
Voltage constant, phase-to-phase	29 mVmin
Phase-phase winding resistance	11.2 Ohm
Phase-phase winding inductance	20.9 mH
Overall mass moment of inertia at power take-off	0.214 kgcm ²
Product weight	1,100 g
Permissible axial shaft load	90 N
Permissible radial shaft load	180 N
Rotor position sensor	Absolute single turn encoder
Rotary position encoder interface	Nikon A format
Rotary position encoder measuring principle	Optical
Rotary position encoder, typical resolution	20 Bit
Rotary position encoder, typical angular accuracy	20 arcmin