

Filter

LF-QS4-D-5M-MICRO-H

Part number: 526306



Classic - do not use for new projects

Connection plate with push-in connector, semiautomatic condensate drain

Modern alternatives can be found by entering the first four characters of the type code in the search field.

Type to be discontinued. Available until 2023. See Support Portal for alternative products.

FESTO



Data sheet

| Feature | Value |
|---|---|
| Size | Micro |
| Series | D |
| Assembly position | Vertical +/- 5° |
| Grade of filtration | 5 µm |
| Condensate drain | semi-automatic |
| Design structure | Sintered filter with centrifugal separator |
| Max. condensate volume | 3 cm ³ |
| Working pressure | 1 ... 10 bar |
| Standard nominal flow rate | 170 l/min |
| Operating medium | Compressed air to ISO 8573-1:2010 [-:9:-] Inert gases |
| Corrosion resistance classification CRC | 2 - Moderate corrosion stress |
| Air purity class at output | Compressed air in accordance with ISO8573-1:2010 [6:8:4] Inert gases |
| Medium temperature | -10 ... 60 °C |
| Ambient temperature | -10 ... 60 °C |
| Product weight | 64 g |
| Mounting type | Line installation with accessories Optional |
| Pneumatic connection, port 1 | QS-4 |
| Pneumatic connection, port 2 | QS-4 |
| Materials note | Conforms to RoHS |
| Material filter | PE |
| Material housing | Aluminum die cast |
| Material bowl | PC |