

Filter regulator MS4N-LFR-1/8-D6-ERM-AS-Z

Part number: 531224

FESTO

7 bar maximum output pressure, 40 µm filter, with pressure gauge, lockable regulator head, plastic bowl with plastic bowl guard, manual condensate drain, direction of flow: from right to left.



Data sheet

| Feature | Value |
|---|---|
| Size | 4 |
| Series | MS |
| Actuator lock | with accessories, lockable |
| Assembly position | Vertical +/- 5° |
| Grade of filtration | 40 µm |
| Condensate drain | manual rotary |
| Design structure | Filter regulator with pressure gauge |
| Max. condensate volume | 19 ml |
| Controller function | Output pressure constant with secondary exhaust with return flow |
| Bowl guard | Plastic guard |
| Pressure gauge | with pressure gauge |
| Pressure control range | 0.3 ... 7 bar |
| Inlet pressure 1 | 0.8 ... 14 bar |
| Max. pressure hysteresis | 0.25 bar |
| Standard nominal flow rate | 1,000 l/min |
| Operating medium | Compressed air |
| Corrosion resistance classification CRC | 2 |
| Storage temperature | -10 ... 60 °C |
| Air purity class at output | 5:7:- per DIN ISO 8573-1 |
| Medium temperature | -10 ... 60 °C |
| Ambient temperature | -10 ... 60 °C |
| Product weight | 275 g |
| Mounting type | with accessories Optional Front panel installation Line installation |
| Pneumatic connection, port 1 | NPT1/8-27 |
| Pneumatic connection, port 2 | NPT1/8-27 |
| Materials information for seals | NBR |
| Materials information, housing | Aluminum die cast |
| Materials information for bowl | PC |
| Material information, isolating disc | POM |