


Precision pressure regulator MS6N-LRP


Part number: 538053

FESTO

With NPT thread



Exemplary representation



Data sheet

Overall data sheet – Individual values depend upon your configuration.

Feature	Value
Size	6
Series	MS
Actuator lock	Rotary knob with lock
Assembly position	Any
Design structure	Piloted precision diaphragm regulator
Controller function	Output pressure constant with secondary exhaust
Pressure gauge	Prepared for G1/4 Prepared for G1/8 with pressure sensor with pressure gauge
Operating pressure MPa	0.1 ... 1.4 MPa
Working pressure	1 ... 14 bar
Pressure regulation range	0.05 ... 12 bar
Max. pressure hysteresis	0.02 bar
Flow rate, secondary venting	220 ... 900 l/min
Standard nominal flow rate	800 ... 5,000 l/min
Authorization	c UL us - Recognized (OL)
Operating medium	Compressed air in accordance with ISO8573-1:2010 [7:4:4] Inert gases
Note on operating and pilot medium	Lubricated operation not possible
Corrosion resistance classification CRC	2 - Moderate corrosion stress
PWIS conformity	VDMA24364-B2-L
Storage temperature	-10 ... 60 °C
Medium temperature	-10 ... 60 °C
Ambient temperature	-10 ... 60 °C
Product weight	1,000 g
Mounting type	Front panel installation Line installation with accessories Optional
Pilot air port 12	1/8 NPT
Pneumatic connection, port 1	1/4 NPT 3/8 NPT 1/2 NPT
Pneumatic connection, port 2	1/4 NPT 3/8 NPT 1/2 NPT
Pneumatic connection, port 3	G1/4
Materials note	Conforms to RoHS
Material seals	NBR
Material housing	Aluminum