


# Multi-pin CPV10-VI-P8-M7-C

Part number: 538810  
Classic - do not use for new projects

FESTO

[For valve manifold CPV.](#)

Modern alternatives can be found by entering the first four characters of the type code in the search field.



## Data sheet

Feature	Value
CE symbol (see declaration of conformity)	according to EU-Ex protection guideline (ATEX)
UKCA marking (see declaration of conformity)	To UK EX instructions To UK RoHS instructions
Explosion protection certification outside the EU	EPL Db (GB) EPL Db (IEC-EX) EPL Dc (IEC-EX) EPL Gb (GB) EPL Gb (IEC-EX) EPL Gc (IEC-EX)
Certificate issuing department	IECEX TUR 12.0002X TÜV 06 ATEX 7334 X TÜV 21 UKEX 7013 X
ATEX category Gas	II 2G
ATEX category Dust	II 2D
Explosion ignition protection type Gas	Ex eb IIC Gb
Explosion ignition protection type Dust	Ex tb IIIC Db
Explosion-proof ambient temperature	-10°C ≤ Ta ≤ +60°C
Corrosion resistance classification CRC	2 - Moderate corrosion stress
PWIS conformity	VDMA24364-B1/B2-L
Product weight	460 g
Materials note	Conforms to RoHS Halogen-free Free of copper
Material seals	NBR
Material plate	Wrought Aluminum alloy