

Filter MS12-LF

Part number: 535023

FESTO

For manifold assembly, with G thread.



Exemplary representation

Data sheet

Overall data sheet – Individual values depend upon your configuration.

Feature	Value
Size	12
Series	MS
Assembly position	Vertical +/- 5°
Design structure	Sintered filter with centrifugal separator
Working pressure	0.8 ... 20 bar
Operating medium	Compressed air to ISO 8573-1:2010 [-:9:-] Compressed air to ISO 8573-1:2010 [7:9:-] Inert gases
PWIS conformity	VDMA24364-B1/B2-L
Storage temperature	-10 ... 60 °C
Medium temperature	-10 ... 60 °C
Ambient temperature	-10 ... 60 °C
Mounting type	Line installation with accessories Optional
Material housing	Aluminum die cast
Material bowl	Wrought Aluminum alloy