

Activated carbon filter MS12N-LFX

Part number: 535046

FESTO

With NPT thread



Exemplary representation

Data sheet

Overall data sheet – Individual values depend upon your configuration.

Feature	Value
Size	12
Series	MS
Assembly position	Vertical +/- 5°
Design structure	Active carbon filter
Working pressure	0 ... 20 bar
Operating medium	Compressed air in accordance with ISO8573-1:2010 [1:4:2] Inert gases
Corrosion resistance classification CRC	2 - Moderate corrosion stress
PWIS conformity	VDMA24364-B2-L
Storage temperature	-10 ... 60 °C
Air purity class at output	Compressed air to ISO 8573-1:2010 [1:4:1]
Medium temperature	5 ... 30 °C
Residual oil content	0.003 mg/m ³
Ambient temperature	-10 ... 60 °C
Mounting type	Line installation with accessories Optional
Materials note	Conforms to RoHS
Material filter	Active carbon
Material housing	Aluminum die cast
Material bowl	Wrought Aluminum alloy