


Multi-pin CPV14-VI-P8-1/8-C

Part number: 539501
Classic - do not use for new projects

FESTO

[For valve manifold CPV.](#)

Modern alternatives can be found by entering the first four characters of the type code in the search field.



Data sheet

Feature	Value
CE symbol (see declaration of conformity)	according to EU-Ex protection guideline (ATEX)
UKCA marking (see declaration of conformity)	To UK EX instructions To UK RoHS instructions
Explosion protection certification outside the EU	EPL Db (GB) EPL Db (IEC-EX) EPL Dc (IEC-EX) EPL Gb (GB) EPL Gb (IEC-EX) EPL Gc (IEC-EX)
Certificate issuing department	IECEX TUR 12.0002X TÜV 06 ATEX 7334 X TÜV 21 UKEX 7013 X
ATEX category Gas	II 2G
ATEX category Dust	II 2D
Explosion ignition protection type Gas	Ex eb IIC Gb
Explosion ignition protection type Dust	Ex tb IIIC Db
Explosion-proof ambient temperature	-10°C ≤ Ta ≤ +60°C
Corrosion resistance classification CRC	2 - Moderate corrosion stress
PWIS conformity	VDMA24364-B1/B2-L
Product weight	920 g
Materials note	Conforms to RoHS Halogen-free Free of copper
Material seals	NBR
Material plate	Wrought Aluminum alloy