

# Receiver



## SOEG-E-M18W-PA-S-2L

Part number: 537696  
Product to be discontinued

FESTO

Round design, with 90° angled beam

Type to be discontinued. Available until 2024. See Support Portal for alternative products.



## Data sheet

Feature	Value
Design	Round
Conforms to standard	EN 60947-5-2
Authorization	RCM Mark c UL us - Listed (OL)
CE symbol (see declaration of conformity)	according to EU-EMV guideline
Measured variable	Position
Measuring principle	Optoelectronic
Measurement method	Through-beam sensor Receiver
Working range	20,000 mm
Ambient temperature	-25 ... 55 °C
Switch output	PNP
Switching element function	Antivalent
Max. switching frequency	1,000 Hz
Max. output current	200 mA
Voltage drop	≤ 2 V
Short circuit strength	Pulsing
Operating voltage range DC	10 ... 36 V
Residual ripple	20 %
Idle current	10 mA
Polarity protected	for all electrical connections
Electrical connection	4-pin M12x1 Plug
Size	M18x1
Mounting type	with lock nut
Tightening torque	20 Nm
Product weight	57 g
Material housing	Brass Chromed-plated
Material of union nut	Brass Chromed-plated
Operating status display	Yellow LED
Operating reserve display	Green LED
Ambient temperature with flexible cable installation	-5 ... 55 °C
Protection class	IP65 IP67
Corrosion resistance classification CRC	1 - Low corrosion stress
PWIS conformity	VDMA24364-B2-L