



Diffuse light sensor SOEL-RTH-Q20-NP-S-2L-TI

Part number: 537728
Product to be discontinued

FESTO

With background suppression, block design
Type to be discontinued. Available until 2020. See Support Portal for alternative products.



Data sheet

Feature	Value
Design	Block design
Conforms to standard	EN 60947-5-2
Authorization	RCM Mark c UL us - Listed (OL)
CE symbol (see declaration of conformity)	according to EU-EMV guideline
Materials note	Free of copper and PTFE
Measured variable	Position
Measuring principle	Optoelectronic
Measurement method	Diffuse reflection sensor with background suppression
Type of light	Laser Red
Max. spot diameter	0.7 mm in focus
Working range	30 ... 110 mm
Ambient temperature	-20 ... 60 °C
Max. grey tone shift	7 %
Reference material	18 %
Switch output	NPN
Switching element function	Switchable
Max. switching frequency	1,000 Hz
Max. output current	100 mA
Voltage drop	≤ 2.4 V
Short circuit strength	Pulsing
Operating voltage range DC	10 ... 30 V
Residual ripple	10 %
Idle current	30 mA
Polarity protected	for all electrical connections
Electrical connection	Plug M8x1 4-pin
Size	20x32x12 mm
Mounting type	with through hole
Product weight	36 g
Material housing	ABS
Operating status display	Yellow LED
Operating reserve display	Green LED
Setting options	Teach-In Teach-in via electrical connection
Setting range lower limit	30 mm
Upper limit of adjustment range	110 mm
Ambient temperature with flexible cable installation	-5 ... 60 °C
Protection class	IP67
Corrosion resistance classification CRC	2 - Moderate corrosion stress
Laser protection class	2