



Proximity Sensor SIED-M18NB-ZS-K-L

Part number: 538276

FESTO

With cable, non-flush mounting



Data sheet

Feature	Value
Design	Round
Conforms to standard	EN 60947-5-2
Authorization	RCM Mark c UL us - Listed (OL)
CE symbol (see declaration of conformity)	according to EU-EMV guideline according to EU low voltage guideline
Measuring principle	Inductive
Nominal switching distance	8 mm
Guaranteed switching distance	6.5 mm
Reduction factors	Aluminum = 0.4 Stainless steel, St 18/8 = 0.7 Copper = 0.3 Brass = 0.4 Steel, St 37 = 1.0
Ambient temperature	-25 ... 85 °C
Repetition accuracy	0.2 mm
Switch output	Non-contacting 2-wire
Switching element function	Normally open contact
Hysteresis	0.03 ... 1.9 mm
Max. switching frequency, DC	340 Hz
Max. switching frequency, AC	25 Hz
Max. output current	300 mA
Voltage drop	≤ 8 V
Minimum load current	5 mA
Short circuit strength	No
Operating voltage range AC	20 ... 265 V
Operating voltage range DC	20 ... 320 V
Line frequency	50 Hz
Idle current	≤ 1.5 mA
Polarity protected	for all electrical connections
Electrical connection	2-core Cable
Cable length	2.5 m
Material cable sheath	TPE-U(PUR)
Material insulation	PVC
Size	M18
Mounting type	with lock nut
Tightening torque	30 Nm
Type of installation	not flush
Product weight	110 g
Material housing	Brass PA Nickel plated
Operating status display	Yellow LED
Ambient temperature with flexible cable installation	-5 ... 50 °C
Protection class	IP67
Corrosion resistance classification CRC	1 - Low corrosion stress
PWIS conformity	VDMA24364-B2-L