



Proximity Sensor SIEF-M18B-NS-S-L-WA

Part number: 538302
Product to be discontinued

FESTO

With plug, flush mounting

Type to be discontinued. Available until 2025. See Support Portal for alternative products.



Data sheet

Feature	Value
Design	Round
Conforms to standard	EN 60947-5-2
Authorization	RCM Mark c UL us - Listed (OL)
CE symbol (see declaration of conformity)	according to EU-EMV guideline
Measuring principle	Inductive
Nominal switching distance	5 mm
Guaranteed switching distance	4.05 mm
Reduction factors	Aluminum = 1.0 Stainless steel, St 18/8 = 1.0 Copper = 1.0 Brass = 1.0 Steel, St 37 = 1.0
Ambient temperature	-30 ... 85 °C
Repetition accuracy	0.1 mm
Switch output	NPN
Switching element function	Normally open contact
Hysteresis	0.15 ... 0.75 mm
Max. switching frequency, DC	2,500 Hz
Max. output current	200 mA
Voltage drop	≤ 1.8 V
Short circuit strength	Pulsing
Operating voltage range DC	10 ... 30 V
Residual ripple	10 %
Idle current	≤ 15 mA
Polarity protected	for all electrical connections
Electrical connection	3-pin Fixcon M12x1 Plug
Size	M18
Mounting type	with lock nut
Tightening torque	15 Nm
Type of installation	flush
Product weight	48 g
Material housing	Brass PBT PTFE coated
Operating status display	Yellow LED
Protection class	IP67
Interference immunity to magnetic fields	DC and AC magnetic field
Corrosion resistance classification CRC	0 - No corrosion stress