


# Proximity Sensor SIED-M30NB-ZS-K-L-PA

Part number: 538339

FESTO

With cable, non-flush mounting



## Data sheet

Feature	Value
Design	Round
Conforms to standard	EN 60947-5-2
Authorization	RCM Mark c UL us - Listed (OL)
CE symbol (see declaration of conformity)	according to EU-EMV guideline according to EU low voltage guideline
Measuring principle	Inductive
Nominal switching distance	15 mm
Guaranteed switching distance	12.15 mm
Reduction factors	Aluminum = 0.35 to 0.5 Stainless steel, St 18/8 = 0.6 to 1.0 Copper = 0.25 to 0.45 Brass = 0.35 to 0.5 Steel, St 37 = 1.0
Ambient temperature	-25 ... 70 °C
Repetition accuracy	0.3 mm
Switch output	Non-contacting 2-wire
Switching element function	Normally open contact
Hysteresis	0.45 ... 2.25 mm
Max. switching frequency, DC	60 Hz
Max. switching frequency, AC	20 Hz
Max. output current	300 mA
Voltage drop	≤ 6 V
Minimum load current	3 mA
Short circuit strength	No
Operating voltage range AC	20 ... 250 V
Operating voltage range DC	10 ... 300 V
Line frequency	50 ... 60 Hz
Idle current	≤ 1.5 mA
Polarity protected	for all electrical connections
Electrical connection	2-core Cable
Cable length	2.5 m
Material cable sheath	PVC
Material insulation	PVC
Size	M30
Mounting type	with lock nut
Tightening torque	5 Nm
Type of installation	not flush
Product weight	175 g
Material housing	PA-reinforced
Operating status display	Yellow LED
Ambient temperature with flexible cable installation	0 ... 70 °C
Protection class	IP65 IP67
Corrosion resistance classification CRC	4 - Very high corrosion stress