

Plastic tubing


PUN-E-12x1,6-SW-200

Part number: 538464

FESTO

Suitable for use with QS push-in connectors, highly flexible, hydrolysis resistant, micron stable, approved for use in food processing.

Type to be discontinued. Available until 2012.



Data sheet

| Feature | Value |
|--|--|
| Outside diameter | 12 mm |
| Bending radius relevant for flow rate | 80 mm |
| Inside diameter | 8.8 mm |
| Min. bending radius | 36 mm |
| Temperature dependent working pressure | -0.95 ... 8 bar |
| Operating medium | Compressed air in accordance with ISO8573-1:2010 [7:-:-] |
| Food-industry approval | FDA 2002/72/EG |
| Ambient temperature | -35 ... 50 °C |
| Product weight according to length | 0.069 kg/m |
| Color | Black |
| Shore hardness | D 52 +/-3 |
| Materials note | Free of copper and PTFE Conforms to RoHS |
| Materials information for tubing | TPE-U(PU) |