



Parallel gripper HGPC-20-A-G2

Part number: 539272
Product to be discontinued

FESTO

Self-centering, can be used as internal and external gripper, with facility for proximity position sensing, with gripper retention force, closing ...-G2.

Type to be discontinued. Available until 2019. See Support Portal for alternative products.



Data sheet

Feature	Value
Size	20
Stroke per gripper jaw	7 mm
Max. replacement accuracy	≤ 0.2 mm
Max. angular gripper jaw backlash ax,ay	0 deg
Max. gripper jaw backlash Sz	0 mm
Rotationally symmetrical	≤ 0.2 mm
Repetition accuracy, gripper	≤ 0.05 mm
Number of gripper fingers	2
Assembly position	Any
Mode of operation	double-acting
Gripper function	Parallel
Gripper force back-up	On closing
Design structure	Inclined plane guided motion sequence
Position detection	For proximity sensor
Working pressure	4 ... 8 bar
Max. operating frequency of gripper	4 Hz
Min. opening time at 6 bar	105 ms
Min. closing time at 6 bar	75 ms
Operating medium	Compressed air in accordance with ISO8573-1:2010 [7:4:4]
Note on operating and pilot medium	Lubricated operation possible (subsequently required for further operation)
Corrosion resistance classification CRC	2 - Moderate corrosion stress
Ambient temperature	5 ... 60 °C
Mass moment of inertia	0.274 kgcm ²
Max. force on gripper jaw Fz static	120 N
Max. torque at gripper Mx static	5 Nm
Max. torque at gripper My static	5 Nm
Max. torque at gripper Mz static	5 Nm
Lubrication interval for guide components	10 Mio SP
Max. ground per external gripper finger	80 g
Product weight	477 g
Mounting type	Internal thread and centering sleeve
Pneumatic connection	M5
Materials note	Free of copper and PTFE
Material housing	Zinc die-casting Painted
Material gripper jaws	High alloy steel, non-corrosive