


Multi-pin CPV14-VI-P4-1/8-C

Part number: 539499
Classic - do not use for new projects

FESTO

[For valve manifold CPV.](#)

Modern alternatives can be found by entering the first four characters of the type code in the search field.



Data sheet

| Feature | Value |
|---|--|
| CE symbol (see declaration of conformity) | according to EU-Ex protection guideline (ATEX) |
| UKCA marking (see declaration of conformity) | To UK EX instructions To UK RoHS instructions |
| Explosion protection certification outside the EU | EPL Db (GB) EPL Db (IEC-EX) EPL Dc (IEC-EX) EPL Gb (GB) EPL Gb (IEC-EX) EPL Gc (IEC-EX) |
| Certificate issuing department | IECEX TUR 12.0002X TÜV 06 ATEX 7334 X TÜV 21 UKEX 7013 X |
| ATEX category Gas | II 2G |
| ATEX category Dust | II 2D |
| Explosion ignition protection type Gas | Ex eb IIC Gb |
| Explosion ignition protection type Dust | Ex tb IIIC Db |
| Explosion-proof ambient temperature | -10°C ≤ Ta ≤ +60°C |
| Corrosion resistance classification CRC | 2 - Moderate corrosion stress |
| PWIS conformity | VDMA24364-B1/B2-L |
| Product weight | 650 g |
| Materials note | Conforms to RoHS Halogen-free Free of copper |
| Material seals | NBR |
| Material plate | Wrought Aluminum alloy |